


FC-T1 Cut Sheet



AutomationDirect temperature transmitter, isolated, thermocouple or millivolt input, deg F or deg C, 4-20 mA output, 24 VDC operating voltage, 35mm DIN rail or panel mount, removable screw terminal plugs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FC-T1>

Technical Specifications

Brand	AutomationDirect
Item	Temperature transmitter
Isolation	Isolated
Field Configurable	Yes
Input Thermocouple Signal Type	J, K, T, E, R, S, B, N, C
Input Voltage Signal Range	0-156.25 mVDC, +/- 156.25 mVDC
Programmable Temperature Range	Deg F or deg C
Output Current Signal Range	4-20 mA
Operating Voltage	24 VDC
Housing Material	Plastic
Mounting	35mm DIN rail or panel
Electrical Connection	Removable screw terminal plugs

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document