

FEP5KP1FA8-024M Cut Sheet



Comepi safety switch, tongue (key) interlock, solenoid, 24 VDC to unlock, 90-degree adjustable head, 1200N holding force, (4) N.C. safety output(s), thermoplastic body, (3) M20 x 1.5mm cable entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FEP5KP1FA8-024M>

Technical Specifications

| | |
|---------------------------|-------------------------------|
| Brand | Comepi |
| Item | Safety switch |
| Actuator Type | Tongue (key) interlock |
| Lock Type | Solenoid, 24 VDC to unlock |
| Head Type | 90-degree adjustable |
| Holding Force | 1200N |
| Safety Output Type | (4) N.C. |
| Housing Size | 40 x 190 x 42mm |
| Body Material | Thermoplastic |
| Head Material | Thermoplastic |
| IP Rating | IP65 |
| Connection | (3) M20 x 1.5mm cable entries |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E189258 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |