

FLS-HL-300 Cut Sheet



ProSense float liquid level switch, horizontal side mount, 5.81in insertion length, 1in diameter float, 304 stainless steel, Teflon, Ceramic wetted parts, -40 to 302 deg F, 1in male NPT process connection, SPDT reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-HL-300>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Horizontal side
Insertion Length	5.81in
Float	1in diameter
Process Connection	1in male NPT
Wetted Parts	304 stainless steel, Teflon, Ceramic
Process Temperature	-40 to 302 deg F
Output	SPDT reed switch, N.O./N.C. selectable
Electrical Connection	24in 22AWG lead wires with stripped ends
Conductor	316L stainless steel
Insulation Material	

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FLS-HL-300.pdf>
See store item page for other formats.