

FLS-HM-200 Cut Sheet



ProSense float liquid level switch, horizontal side mount, 4.6in insertion length, 0.63in diameter float, 316 stainless steel wetted parts, -40 to 392 deg F, dual 1/2in male NPT process connection, SPST reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-HM-200>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Horizontal side
Insertion Length	4.6in
Float	0.63in diameter
Process Connection	Dual 1/2in male NPT
Wetted Parts	316 stainless steel
Process Temperature	-40 to 392 deg F
Output	SPST reed switch, N.O./N.C. selectable
Electrical Connection	24in 22AWG lead wires with stripped ends
Conductor Insulation Material	Teflon

Agency Approvals

UL Listed File #	None
UL Recognized File #	E320431
UL Hazardous File #	E366154
CE	View CE declarations
CSA File #	259726
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document