

# FLS-HM-500 Cut Sheet



ProSense float liquid level switch, horizontal side mount, 2.75in insertion length, 0.65in diameter float, polybutylene wetted parts, -40 to 266 deg F, 1/2in male NPT process connection, SPST reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-HM-500>

## Technical Specifications

|                               |   |
|-------------------------------|---|
| <b>Brand</b>                  | ProSense  |
| <b>Item</b>                   | Level switch  |
| <b>Sensor Type</b>            | Float   |
| <b>Media Type</b>             | Liquid  |
| <b>Mounting</b>               | Horizontal side   |
| <b>Insertion Length</b>       | 2.75in  |
| <b>Float</b>                  | 0.65in diameter   |
| <b>Process Connection</b>     | 1/2in male NPT  |
| <b>Wetted Parts</b>           | Polybutylene  |
| <b>Process Temperature</b>    | -40 to 266 deg F  |
| <b>Output</b>                 | SPST reed switch, N.O./N.C. selectable                              |
| <b>Electrical Connection</b>  | 0.25" x 0.032" quick connect terminals                              |
| <b>Additional Information</b> | Not for use in hot water at temperatures above 149 deg F (65 deg C) |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E320431                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |