

# FLS-HM-600 Cut Sheet



ProSense float liquid level switch, horizontal side mount, 2.96in insertion length, 0.65in diameter float, polybutylene wetted parts, -40 to 266 deg F, 5/8-11 male UNC with washer and nut process connection, SPST reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-HM-600>

## Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Horizontal side
Insertion Length	2.96in
Float	0.65in diameter
Process Connection	5/8-11 male UNC with washer and nut

Wetted Parts	Polybutylene
Process Temperature	-40 to 266 deg F
Output	SPST reed switch, N.O./N.C. selectable
Electrical Connection	24in 22AWG lead wires with stripped ends
Conductor Insulation Material	316L stainless steel
Additional Information	Not for use in hot water at temperatures above 149 deg F (65 deg C)

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E320431
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/FLS-HM-600.pdf>  
See store item page for other formats.