

FLS-VD-400 Cut Sheet



ProSense float liquid level switch, vertical top mount, 2in insertion length, 0.9in diameter float, 316 stainless steel wetted parts, -40 to 302 deg F, 3/4in male NPT pipe plug process connection, SPST reed switch, N.O.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-VD-400>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Vertical top
Insertion Length	2in
Float	0.9in diameter
Process Connection	3/4in male NPT pipe plug
Wetted Parts	316 stainless steel
Process Temperature	-40 to 302 deg F
Output	SPST reed switch, N.O.
Electrical Connection	72in cable with 22AWG conductors
Jacket Material	Halar
Additional Information	High level switch for 55 gallon drums

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FLS-VD-400.pdf>
See store item page for other formats.