

FLS-VD-500 Cut Sheet



ProSense float liquid level switch, vertical top mount, 32in insertion length, 0.9in diameter float, 316 stainless steel wetted parts, -40 to 302 deg F, 3/4in male NPT pipe plug process connection, SPST reed switch, N.C.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-VD-500>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Vertical top
Insertion Length	32in
Float	0.9in diameter
Process Connection	3/4in male NPT pipe plug
Wetted Parts	316 stainless steel
Process Temperature	-40 to 302 deg F
Output	SPST reed switch, N.C.
Electrical Connection	72in cable with 22AWG conductors
Jacket Material	Halar
Additional Information	Low level switch for 55 gallon drums

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document