

FLS-VD-600 Cut Sheet



ProSense float liquid level switch, vertical top mount, 32in insertion length, 0.9in diameter float, 316 stainless steel wetted parts, -40 to 302 deg F, 3/4in male NPT pipe plug process connection, (1) SPST reed switch, N.O. and (1) SPST reed switch, N.C.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-VD-600>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Vertical top
Insertion Length	32in
Float	0.9in diameter
Process Connection	3/4in male NPT pipe plug
Wetted Parts	316 stainless steel
Process Temperature	-40 to 302 deg F
Output	(1) SPST reed switch, N.O. and (1) SPST reed switch, N.C.
Electrical Connection	72in cable with 22AWG conductors
Jacket Material	Halar
Additional Information	High and low level switches for 55 gallon drum

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document