

FLS-VL-010 Cut Sheet



ProSense float liquid level switch, vertical top mount, 1.69in insertion length, 1.44in diameter slosh shield float, polypropylene wetted parts, -40 to 221 deg F, 1/8in male NPT process connection, SPST reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-VL-010>

Technical Specifications

| | |
|-----------------------|--|
| Brand | ProSense |
| Item | Level switch |
| Sensor Type | Float |
| Media Type | Liquid |
| Mounting | Vertical top |
| Insertion Length | 1.69in |
| Float | 1.44in diameter slosh shield |
| Process Connection | 1/8in male NPT |
| Wetted Parts | Polypropylene |
| Process Temperature | -40 to 221 deg F |
| Output | SPST reed switch, N.O./N.C. selectable |
| Electrical Connection | 24in 22AWG lead wires with stripped ends |
| Conductor | 316 stainless steel |
| Insulation Material | |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E320431 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 259726 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FLS-VL-010.pdf>
See store item page for other formats.