

# FLS-VM-400 Cut Sheet



ProSense float liquid level switch, vertical top mount, 1.63in insertion length, 1.13in diameter float, 316 stainless steel wetted parts, -40 to 392 deg F, 1/8in male NPT process connection, SPST reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-VM-400>

## Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Vertical top
Insertion Length	1.63in
Float	1.13in diameter
Process Connection	1/8in male NPT
Wetted Parts	316 stainless steel
Process Temperature	-40 to 392 deg F
Output	SPST reed switch, N.O./N.C. selectable
Electrical Connection	24in 22AWG lead wires with stripped ends
Conductor	316L stainless steel
Insulation Material	

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E320431
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	259726
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FLS-VM-400.pdf>  
See store item page for other formats.