

# FMM200-1002 Cut Sheet



ProSense liquid flow meter, magnetic-inductive, 2in female NPT process connection, 0 to 158.5 GPM, -4 to 176 deg F, Output: analog, Output 2: analog.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FMM200-1002>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Flow meter
<b>Media Type</b>	Liquid
<b>Sensing Type</b>	Magnetic-inductive
<b>Process Connection</b>	2in female NPT
<b>Measuring Range</b>	0 to 158.5 GPM
<b>Measuring Range 2</b>	-4 to 176 deg F
<b>Output</b>	Analog, 4-20 mA
<b>Output 2</b>	Analog, 4-20 mA
<b>Operating Voltage</b>	18-32 VDC
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E320431
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FMM200-1002.pdf>  
See store item page for other formats.