

# FMM75-1001 Cut Sheet



ProSense liquid flow meter, magnetic-inductive, 3/4in female NPT process connection, 0 to 13.2 GPM, -4 to 176 deg F, 0.01 to 30,000,000 gallons, Output: switch or pulse, Output 2: switch, analog or reset input.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FMM75-1001>

## Technical Specifications

Brand	ProSense
Item	Flow meter
Media Type	Liquid
Sensing Type	Magnetic-inductive
Process Connection	3/4in female NPT
Measuring Range	0 to 13.2 GPM
Measuring Range 2	-4 to 176 deg F
Measuring Range 3	0.01 to 30,000,000 gallons
Output	Switch (N.O./N.C.) or pulse, PNP/NPN selectable
Output 2	Switch (N.O./N.C.) or analog or reset input, PNP/NPN selectable or 4-20 mA/0-10 VDC
Operating Voltage	19-30 VDC
Electrical Connection	4-pin M12 quick-disconnect
Additional Information	Purchase cable separately

## Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FMM75-1001.pdf>  
See store item page for other formats.