

# FMR10-CAQBMVCEVEE2 Cut Sheet



Endress+Hauser Micropilot pulsed radar liquid level sensor, 8m (26.3) or 12m (39.4 ft) with flooding protection tube sensing range, 4-20mA, 10.5-30 VDC operating voltage, 1-1/2in male NPT process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FMR10-CAQBMVCEVEE2>

## Technical Specifications

<b>Brand</b>	Endress+Hauser
<b>Series</b>	Micropilot
<b>Item</b>	Level sensor
<b>Sensor Type</b>	Pulsed radar
<b>Media Type</b>	Liquid
<b>Sensing Range</b>	8m (26.3) or 12m (39.4 ft) with flooding protection tube
<b>Output</b>	4-20mA
<b>Operating Voltage</b>	10.5-30 VDC
<b>Housing Rating</b>	NEMA 6P (IP68)
<b>Process Connection</b>	1-1/2in male NPT
<b>Electrical Connection</b>	1in male NPT with 10m/32ft cable
<b>Requires</b>	An Android or iOS device with Bluetooth connectivity and SmartBlue App (free download from the Google Play Store and Apple App Store) is required for full sensor configuration

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	053988
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>