

# FR100806HW Cut Sheet



AttaBox Freedom series enclosure, NEMA 1/3/3S/4X/12/13, 10 x 8 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FR100806HW>

## Technical Specifications

|                          |                              |
|--------------------------|------------------------------|
| Brand                    | AttaBox                      |
| Item                     | Enclosure                    |
| Series                   | Freedom                      |
| Subpanel                 | Purchase subpanel separately |
| Slope Top                | No                           |
| NEMA Rating              | 1/3/3S/4X/12/13              |
| IP Rating                | IP66                         |
| Nominal Enclosure Height | 10in                         |
| Nominal Enclosure Width  | 8in                          |
| Nominal Enclosure Depth  | 6in                          |
| Mounting                 | Wall                         |

|                           |                                         |
|---------------------------|-----------------------------------------|
| Integral Mounting Feet    | No                                      |
| Integral Mounting Flange  | No                                      |
| Dual Access               | No                                      |
| Knockouts                 | No                                      |
| Material                  | Fiberglass reinforced polyester         |
| Color                     | Gray                                    |
| Cover Type                | Crowned hinged screw cover              |
| Hinge Type                | Molded hinges with stainless steel pins |
| Number of Hinges Per Door | 2                                       |
| Padlockable               | No                                      |
| Keylocking                | No                                      |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E64358, E362920                        |
| UL Recognized File # | E333478                                |
| UL Hazardous File #  | none                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | LR069014                               |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FR100806HW.pdf>  
See store item page for other formats.