

# FTM20-AM43A Cut Sheet



Endress+Hauser Soliphant vibration rod bulk solids level switch, polyester housing, 8.86in insertion length, 316L stainless steel wetted parts, 1-1/4in male NPT process connection, DPDT relay, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FTM20-AM43A>

## Technical Specifications

<b>Brand</b>	Endress+Hauser
<b>Item</b>	Level switch
<b>Series</b>	Soliphant
<b>Sensor Type</b>	Vibration rod
<b>Media Type</b>	Bulk solids
<b>Mounting</b>	Any orientation
<b>Insertion Length</b>	8.86in
<b>Process Connection</b>	1-1/4in male NPT

<b>Process Temperature</b>	-40 to 302 deg F
<b>Output</b>	DPDT relay
<b>Operating Voltage</b>	19-253 VAC and 19-55 VDC
<b>Wetted Parts</b>	316L stainless steel
<b>Electrical Connection</b>	Screw terminals
<b>Housing Material</b>	Polyester
<b>IP Rating</b>	IP66 and IP67
<b>NEMA Rating</b>	4X

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/FTM20-AM43A.pdf>  
See store item page for other formats.