

FXCS-0MMG3 Cut Sheet



Killark control station cover assembly, hazardous location rated, factory sealed, single pushbutton, mushroom, green, push-pull, (1) N.O./ (1) N.C. contact(s), (3) two-sided legend plate(s), legend plate marking "START,STOP / EMERGENCY STOP, RESET / blank, RESET".

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FXCS-0MMG3>

Technical Specifications

Brand	Killark
Item	Control station cover assembly
Application	Hazardous location rated
Factory Sealed	Yes
Housing Material	Aluminum
Control Station Configuration	Single pushbutton
Operator Type	Mushroom
Operator Size	40mm

Operator Color	Green
Action	Push-pull
Contact Type	(1) N.O./ (1) N.C.
Legend Plate Type	(3) two-sided
Legend Plate Marking	START,STOP / EMERGENCY STOP, RESET / blank, RESET
NEMA Rating	3/7/9
Requires	FXB series splice/device box

Agency Approvals

UL Listed File #	E53360
UL Recognized File #	None
UL Hazardous File #	E12379
CE	None
CSA File #	LR11714
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FXCS-0MMG3.pdf>
See store item page for other formats.