


GCBX3-FHC-N3R4-M Cut Sheet



Gladiator flange handle, lever, gray/chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/3R/4. For use with Gladiator 400A and 600A frame MCCBs. Operating mechanism included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GCBX3-FHC-N3R4-M>

Technical Specifications

Brand	Gladiator
Item	Handle
Handle Type	Flange
Handle Style	Lever
Color	Gray/chrome
Mounting	External front
Number Of Positions	2
Lockable Positions	OFF only
Defeatable	Yes
NEMA Rating	3/3R/4
Test Function	No
For Use With	Gladiator 400A and 600A frame MCCBs
Includes	Operating mechanism
Requires	Cable GCBX3-CBL-XX

Agency Approvals

UL Listed File #	E509077
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document