

# GECP-1CH-1-10A Cut Sheet



Gladiator electronic circuit protector, GECP series, adjustable 1-10A, 12/24 VDC, 1 channel(s), adjustable curve, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GECP-1CH-1-10A>

## Technical Specifications

<b>Brand</b>	Gladiator
<b>Item</b>	Circuit protector
<b>Series</b>	GECP
<b>Circuit Breaker Type</b>	Slim
<b>Circuit Type</b>	Supplementary
<b>Current-Limiting</b>	No
<b>Amperage Rating</b>	Adjustable 1-10A
<b>Input voltage range</b>	10-30 VDC
<b>Output Voltage Range</b>	10-30 VDC

<b>Channels</b>	1
<b>Trip Curve</b>	Adjustable curve
<b>Trip Type</b>	Electronic
<b>UL Rating</b>	UL 60947
<b>NEC Class 2</b>	No
<b>HACR Rated</b>	No
<b>Reverse Feed Capable</b>	No
<b>Mounting</b>	35mm DIN rail
<b>Connection</b>	Spring terminals

## Agency Approvals

<b>UL Listed File #</b>	E191072
<b>UL Recognized File #</b>	E530981
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/GECP-1CH-1-10A.pdf>  
See store item page for other formats.