

GECP-1CH-4A Cut Sheet



Gladiator electronic circuit protector, GECP series, 4A, 12/24 VDC, 1 channel(s), slow 1 curve, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GECP-1CH-4A>

Technical Specifications

| | |
|-----------------------------|-------------------|
| Brand | Gladiator |
| Item | Circuit protector |
| Series | GECP |
| Circuit Breaker Type | Slim |
| Circuit Type | Supplementary |
| Current-Limiting | No |
| Amperage Rating | 4A |
| Input voltage range | 10-30 VDC |

| | |
|-----------------------------|------------------|
| Output Voltage Range | 10-30 VDC |
| Channels | 1 |
| Trip Curve | Slow 1 curve |
| Trip Type | Electronic |
| UL Rating | UL 60947 |
| NEC Class 2 | No |
| Mounting | 35mm DIN rail |
| Connection | Spring terminals |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E191072 |
| UL Recognized File # | E530981 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GECP-1CH-4A.pdf>
See store item page for other formats.