

# GFS30-D1C-24-F Cut Sheet



AcuAMP ground fault sensor, fixed core, 5, 10, or 30 mA selectable trip point, relay, SPDT normally de-energized, automatic reset output, 24 VAC/VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GFS30-D1C-24-F>

## Technical Specifications

<b>Brand</b>	AcuAMP
<b>Item</b>	Ground fault sensor
<b>Body Type</b>	Fixed core
<b>Trip Point</b>	5, 10, or 30 mA selectable
<b>Output</b>	Relay, SPDT normally de-energized, automatic reset
<b>Output Rating</b>	1A @ 125 VAC, 2A @ 30 VDC
<b>Operating Voltage</b>	24 VAC/VDC
<b>Mounting</b>	Panel or optional 35mm DIN rail
<b>Electrical Connection</b>	Screw terminals
<b>UL Rating</b>	UL 1053 recognized

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E343037
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GFS30-D1C-24-F.pdf>  
See store item page for other formats.