

GH15DN-3-10B Cut Sheet



AutomationDirect GH15 series IEC contactor, 16A, (3) N.O. power poles, (1) N.O. auxiliary contacts, 240 VAC (60Hz)/220 VAC (50Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GH15DN-3-10B>

Technical Specifications

Brand	AutomationDirect
Item	Contactor
Series	GH15
Contactor Type	IEC
Actuator Type	Magnetic
Amperage Rating	16A
Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O.
Coil Voltage	240 VAC (60Hz)/220 VAC (50Hz)

Agency Approvals

UL Listed File #	E191059
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GH15DN-3-10B.pdf>
See store item page for other formats.