


GI854S Cut Sheet



ifm efector inductive proximity sensor, tubular, 30mm diameter x 65mm body, bronze-plated brass housing, PNP, (2) OSSD, >21.5mm enable zone, non-flush, IP65 IP67 IP68 IP69K, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GI854S>

Technical Specifications

Brand	ifm efector
Item	Proximity sensor
Sensor Type	Inductive
Application	Safety
Shape	Tubular
Housing Size	30mm diameter x 65mm body
Housing Material	Bronze-plated brass
Barrel Type	Threaded
Adjustable	No
Number of Wires	4
Switching Output	PNP
Operation Mode	(2) OSSD
Enable Zone	>21.5mm

Safe Switch-Off Distance	<12mm
Mounting Type	Non-flush
IO-Link Compatible	No
Operating Voltage	8-32 VDC
Operating Temperature	-40 to 85 deg C
Weld Field Immune	No
Chip Immune	No
IP Rating	IP65 IP67 IP68 IP69K
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Fail-Safe SIL 2 PLd, safe state when damped (target present)

Agency Approvals

UL Listed File #	E174191
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GI854S.pdf>
See store item page for other formats.