

GLHL-EX-141020 Cut Sheet



IDEM safety switch, cable-pull interlock, with reset, hazardous location rated, 125m maximum pull cable length, emergency stop, left hand head, (2) N.C. safety output(s), (2) N.O. monitoring output(s), die-cast aluminum body, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GLHL-EX-141020>

Technical Specifications

| | |
|----------------------------------|------------------------------|
| Brand | IDEM |
| Item | Safety switch |
| Actuator Type | Cable-pull interlock |
| Reset | Yes |
| Head Type | Left hand |
| Action | Snap acting switch mechanism |
| Maximum Pull Cable Length | 125m |
| Emergency Stop | Yes |
| Safety Output Type | (2) N.C. |

| | |
|-------------------------------|-------------------------------|
| Monitoring Output Type | (2) N.O. |
| Housing Size | 223 x 110 x 60mm |
| Body Material | Die-cast aluminum |
| IP Rating | IP67 |
| Connection | Pigtail |
| Conductor Size | 24 AWG |
| Cable Length | 9.8ft/3m |
| Includes | (1) tamper-proof T20 Torx bit |
| Application | Hazardous location rated |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GLHL-EX-141020.pdf>
See store item page for other formats.