

# GLHR-141010-BS Cut Sheet



IDEM safety switch, cable-pull interlock, with reset, 125m maximum pull cable length, emergency stop, right hand head, (4) N.C. safety output(s), (2) N.O. monitoring output(s), 110 VAC LED, die-cast aluminum body, (4) 1/2in NPT cable entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GLHR-141010-BS>

## Technical Specifications

<b>Brand</b>	IDEM
<b>Item</b>	Safety switch
<b>Actuator Type</b>	Cable-pull interlock
<b>Reset</b>	Yes
<b>Head Type</b>	Right hand
<b>Action</b>	Snap acting switch mechanism
<b>Maximum Pull Cable Length</b>	125m
<b>Emergency Stop</b>	Yes

<b>Safety Output Type</b>	(4) N.C.
<b>Monitoring Output Type</b>	(2) N.O.
<b>Indicating Type</b>	110 VAC LED
<b>Housing Size</b>	223 x 110 x 60mm
<b>Body Material</b>	Die-cast aluminum
<b>IP Rating</b>	IP67
<b>Connection</b>	(4) 1/2in NPT cable entries
<b>Includes</b>	(1) tamper-proof T20 Torx bit

## Agency Approvals

<b>UL Listed File #</b>	E258676
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GLHR-141010-BS.pdf>  
See store item page for other formats.