

GLHR-EX-141022 Cut Sheet



IDEM safety switch, cable-pull interlock, with reset, hazardous location rated, 125m maximum pull cable length, emergency stop, right hand head, (2) N.C. safety output(s), (2) N.O. monitoring output(s), die-cast aluminum body, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GLHR-EX-141022>

Technical Specifications

Brand	IDEM
Item	Safety switch
Actuator Type	Cable-pull interlock
Reset	Yes
Head Type	Right hand
Action	Snap acting switch mechanism
Maximum Pull Cable Length	125m
Emergency Stop	Yes
Safety Output Type	(2) N.C.

Monitoring Output Type	(2) N.O.
Housing Size	223 x 110 x 60mm
Body Material	Die-cast aluminum
IP Rating	IP67
Connection	Pigtail
Conductor Size	24 AWG
Cable Length	9.8ft/3m
Includes	(1) tamper-proof T20 Torx bit
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GLHR-EX-141022.pdf>
See store item page for other formats.