

GLS-EX-142030 Cut Sheet



IDEM safety switch, cable-pull interlock, with reset, hazardous location rated, 80m maximum pull cable length, emergency stop, (2) N.C. safety output(s), (2) N.O. monitoring output(s), die-cast aluminum body, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GLS-EX-142030>

Technical Specifications

Brand	IDEM
Item	Safety switch
Actuator Type	Cable-pull interlock
Reset	Yes
Action	Snap acting switch mechanism
Maximum Pull Cable Length	80m
Emergency Stop	Yes
Safety Output Type	(2) N.C.
Monitoring Output Type	(2) N.O.

Housing Size	63 x 222 x 54mm
Body Material	Die-cast aluminum
IP Rating	IP67
Connection	Pigtail
Conductor Size	24 AWG
Cable Length	9.8ft/3m
Includes	(1) tamper-proof T20 Torx bit
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GLS-EX-142030.pdf>
See store item page for other formats.