

GLS-SS-EX-144030 Cut Sheet



IDEM safety switch, cable-pull interlock, with reset, hazardous location rated, 100m maximum pull cable length, emergency stop, (2) N.C. safety output(s), (2) N.O. monitoring output(s), 316 stainless steel body, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GLS-SS-EX-144030>

Technical Specifications

Brand	IDEM
Item	Safety switch
Actuator Type	Cable-pull interlock
Reset	Yes
Action	Snap acting switch mechanism
Maximum Pull Cable Length	100m
Emergency Stop	Yes
Safety Output Type	(2) N.C.
Monitoring Output Type	(2) N.O.

Housing Size	65 x 222 x 54 mm
Body Material	316 stainless steel
IP Rating	IP67 IP69K
Connection	Pigtail
Conductor Size	24 AWG
Cable Length	9.8ft/3m
Includes	(1) tamper-proof T20 Torx bit
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GLS-SS-EX-144030.pdf>
See store item page for other formats.