


GN-BP5MA-R Cut Sheet



Metrol limit switch, vacuum, precision touch, 5mm diameter, threaded, 0.5mm pitch, 19mm length, 3mm head, stainless steel, ball plunger, 1N contact force, (1) N.O. contact(s), 1.6ft/0.5m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GN-BP5MA-R>

Technical Specifications

Brand	Metrol	Cable Length	1.6ft/0.5m
Item	Limit switch	Connection	Pigtail
Application	Vacuum	Conductor Size	27 AWG
Switch Type	Precision touch	Stroke	1.0mm
Diameter	5mm	Repeatability	0.01mm
Barrel Type	Threaded	Thread Pitch	0.5mm
Length	19mm	Material	Stainless steel
Head Type	3mm	Head Material	Stainless steel
Actuator Type	Ball plunger	IP Rating	IP40
Contact Force	1N	Operating Temperature	0 to 120 deg C
Contact Type	(1) N.O.	Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GN-BP5MA-R.pdf>
See store item page for other formats.