

# GPB1-130P1-16S Cut Sheet



Gladiator enclosed terminal block, finger-safe, 130A, 1-pole, line side: 2 (screw) openings accept 1 AWG to 8 AWG & 2 openings accept 6 AWG to 16 AWG, load side: 12 openings accept 8 AWG to 16 AWG, DIN rail or panel mount, UL 1059 recognized.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GPB1-130P1-16S>

## Technical Specifications

|                            |  |
|----------------------------|--|
| <b>Brand</b>               | Gladiator  |
| <b>Item</b>                | Terminal block   |
| <b>Terminal Block Type</b> | Enclosed   |
| <b>Modular</b>             | No   |
| <b>Finger-safe</b>         | Yes  |
| <b>Amperage Rating</b>     | 130A   |
| <b>Number of Poles</b>     | 1  |
| <b>Line Side Openings</b>  | 2 (screw) openings accept 1 AWG to 8 AWG & 2 openings accept 6 AWG to 16 AWG |
| <b>Load Side Openings</b>  | 12 openings accept 8 AWG to 16 AWG   |
| <b>Mounting</b>            | DIN rail or panel  |
| <b>SCCR Rating</b>         | 100kA SCCR   |
| <b>UL Rating</b>           | UL 1059 recognized   |
| <b>IP Rating</b>           | IP20   |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Recognized File #</b> | E179129                                |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 606611                                 |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/GPB1-130P1-16S.pdf>  
See store item page for other formats.