

# GPB2-175P1-10L Cut Sheet



Gladiator enclosed terminal block, finger-safe, 175A, 1-pole, line side: 2 openings accept 2/0 AWG to 6 AWG, load side: 10 openings accept 6–14 AWG, DIN rail or panel mount, UL 1059 recognized.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GPB2-175P1-10L>

## Technical Specifications

<b>Brand</b>	Gladiator
<b>Item</b>	Terminal block
<b>Terminal Block Type</b>	Enclosed
<b>Modular</b>	Yes
<b>Finger-safe</b>	Yes
<b>Amperage Rating</b>	175A
<b>Number of Poles</b>	1
<b>Line Side Openings</b>	2 openings accept 2/0 AWG to 6 AWG
<b>Load Side Openings</b>	10 openings accept 6–14 AWG
<b>Mounting</b>	DIN rail or panel
<b>SCCR Rating</b>	100 kA SCCR
<b>UL Rating</b>	UL 1059 recognized
<b>IP Rating</b>	IP20

## Agency Approvals

<b>UL Recognized File #</b>	E179129
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	609999
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/GPB2-175P1-10L.pdf>  
See store item page for other formats.