

GR-REC4 Cut Sheet



Gladiator quad straight blade receptacle, 15A, 125 VAC, 1-phase, 2-pole, 3-wire, glass fiber reinforced polyamide housing, panel or 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GR-REC4>

Technical Specifications

Brand	Gladiator
Item	Receptacle
Receptacle Type	Quad
Wiring Device Type	Straight blade
Self-grounding	No
Amperage Rating	15A
Voltage Rating	125 VAC
Number of Phases	1
Number of Poles	2

Number of Wires	3
Wire Size	14-12 AWG solid or stranded
Copper Wire Only	Yes
Configuration	NEMA 5-15
Housing Material	Glass fiber reinforced polyamide
Mounting	Panel or 35mm DIN rail
Color	Black
Additional Information	For laptop computers and test equipment

Agency Approvals

UL Listed File #	None
UL Recognized File #	E531313
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GR-REC4.pdf>
See store item page for other formats.