

# GSD1-24-15N4X-R Cut Sheet



IronHorse GSD1 series DC reversing drive, 12/24 VDC, 1-phase, 1/50hp at 12 VDC and 5/16hp at 24 VDC, 15A, NEMA 4X, wall mount, built-in reverse, potentiometer input, PWM output.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GSD1-24-15N4X-R>

## Technical Specifications

<b>Brand</b>	IronHorse
<b>Item</b>	Drive
<b>Controller Type</b>	Reversing
<b>Series</b>	GSD1
<b>Voltage Type</b>	DC
<b>Number of Input Phases</b>	1
<b>Nominal Drive Input Voltage</b>	12/24 VDC
<b>Nominal Drive Output Voltage</b>	Output up to 12/24 VDC
<b>Horsepower by Voltage</b>	1/50hp at 12 VDC and 5/16hp at 24 VDC
<b>Amperage Rating</b>	15A
<b>Variable Torque Amperage Rating</b>	500 mA - 15A
<b>Control Mode</b>	DC
<b>Safe Torque Off (STO)</b>	No
<b>Temperature Rating</b>	-10 to 40 deg C

<b>Enclosure Type</b>	NEMA 4X
<b>IP Rating</b>	IP67
<b>Mounting</b>	Wall
<b>Input Signal</b>	Potentiometer input
<b>Relay Configuration</b>	(1) Form C (SPDT) relay
<b>On/Off Switch</b>	No
<b>Shunt Field Supply</b>	No
<b>Output Type</b>	PWM output
<b>Reverse Capability</b>	Built-in
<b>Output Frequency Range</b>	DC
<b>Connector Type</b>	Screw terminals
<b>SCCR Rating</b>	SCCR exempt
<b>For Use With</b>	Permanent magnet DC, shunt wound DC and universal motors
<b>Includes</b>	Mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GSD1-24-15N4X-R.pdf>  
See store item page for other formats.