

GSDA-PU2E Cut Sheet



IronHorse encoder, 5-24 VDC, NPN open collector output, 1/10/20 ppr, 61mm diameter body, NEMA 12, IP52, 6ft cable length, pigtail. For use with GSD8 series DC drives. Mounting hardware and (3) magnets included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GSDA-PU2E>

Technical Specifications

Brand	IronHorse
Item	Encoder
Replacement	No
Voltage Rating	5-24 VDC
Encoder Output Type	NPN open collector
Encoder Resolution	1/10/20 ppr
Shaft Type	Hollow
Frequency Response	80 Hz/800 Hz/1.6 kHz
Speed Rating	5000rpm

Flange Mount	No
Encoder Body Diameter	61mm
Housing Material	Plastic
NEMA Rating	12
IP Rating	IP52
Cable Length	6ft
Connector Type	Pigtail
For Use With	GSD8 series DC drives
Includes	Mounting hardware and (3) magnets

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GSDA-PU2E.pdf>
See store item page for other formats.