

GVP-311CL-24D Cut Sheet



NITRA solenoid valve, 3-way, 2-position, N.C., single latching solenoid spring return, 10mm wide body, Cv=0.013, 24 VDC, miniature pin plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GVP-311CL-24D>

Technical Specifications

Brand	NITRA
Series	Miniature solenoid valves (GVP)
Item	Valve
Working Fluid	Air
Valve Type	Solenoid directional control
Port Quantity	3-way
Number Of Positions	2
Valve Configuration	N.C.
Action	Single latching solenoid spring return
Body Material	Glass-filled nylon
Body Width	10mm
Mounting	Optional manifold

Stackable	No
Manual Override Type	Momentary
Flow Coefficient	0.013
Maximum Operating Pressure	105 psi
Minimum Operating Pressure	0 psi
Operating Voltage	24 VDC
Electrical Connection	Miniature pin plug
Indicating Type	LED indication
Form Factor	Miniature
Includes	Gasket and mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GVP-311CL-24D.pdf>
See store item page for other formats.