

# GVP-3C1F-TD Cut Sheet



NITRA manual valve, 3-port (3-way), 2-position, N.C., toggle style actuator, detented, 90-degree ports, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), (1) vent hole exhaust(s), Cv=0.23, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GVP-3C1F-TD>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Valve
<b>Working Fluid</b>	Air
<b>Valve Type</b>	Manual directional control
<b>Port Quantity</b>	3-port (3-way)
<b>Number Of Positions</b>	2
<b>Valve Configuration</b>	N.C.
<b>Operator Type</b>	Toggle style actuator
<b>Action</b>	Detented
<b>Body Material</b>	Anodized aluminum
<b>Mounting</b>	Through panel
<b>Inlet Port</b>	1/8in female NPT
<b>Outlet Port</b>	1/8in female NPT
<b>Exhaust Port</b>	(1) vent hole
<b>Port Orientation</b>	90-degree
<b>Stackable</b>	No
<b>Flow Coefficient</b>	0.23
<b>Maximum Operating Pressure</b>	125 psi
<b>Minimum Operating Pressure</b>	0 psi
<b>Form Factor</b>	Standard
<b>Includes</b>	Mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>