

GVS-3C1F-TD Cut Sheet



NITRA manual valve, 3-port (3-way), 2-position, N.C., toggle style actuator, detented, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), vent hole exhaust(s), Cv=0.42, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GVS-3C1F-TD>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air
Valve Type	Manual directional control
OSHA Compliant	No
Port Quantity	3-port (3-way)
Number Of Positions	2
Valve Configuration	N.C.
Operator Type	Toggle style actuator
Action	Detented
Body Material	Anodized aluminum
Mounting	Through panel
Inlet Port	1/8in female NPT
Outlet Port	1/8in female NPT
Exhaust Port	Vent hole
Stackable	No
Flow Coefficient	0.42
Maximum Operating Pressure	126 psi
Minimum Operating Pressure	-26in Hg
Form Factor	Standard
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document