

GVS-520F-PB Cut Sheet



NITRA pneumatic manual valve, 5-port (4-way), 2-position, pushbutton, spring return, #10-32 female UNF inlet(s), #10-32 female UNF outlet(s), #10-32 female threaded exhaust(s), Cv=0.23, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GVS-520F-PB>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air or inert gas
Valve Type	Manual directional control
Port Quantity	5-port (4-way)
Number Of Positions	2
Operator Type	Pushbutton
Action	Spring return
Body Material	Anodized aluminum
Mounting	Through panel

Inlet Port	#10-32 female UNF
Outlet Port	#10-32 female UNF
Exhaust Port	#10-32 female threaded
Stackable	No
Flow Coefficient	0.23
Maximum Operating Pressure	126 psi
Minimum Operating Pressure	0 psi
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GVS-520F-PB.pdf>
See store item page for other formats.