

H20FSSG0 Cut Sheet



WON H20 series standard bearing block, full ball recirculating bearing, flanged, end seal and inside seal, carbon steel. For use with H20 series rails.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H20FSSG0>

Technical Specifications

Brand	WON
Item	Standard bearing block
Series	H20
Bearing Type	Full ball recirculating bearing
Block Type	Flanged
Seal Type	End seal and inside seal
Material	Carbon steel
Precision Class	Moderate precision
Bearing Pre-load	Normal preload
Mass	410g
Static Load Rating (CO)	23900N

Dynamic Load Rating (C)	14900N
Pitch Moment Load Rating (Mp)	221 N-m
Pitch Moment Load Rating, 2 Bearings (Mp2)	1049 N-m
Yaw Moment Load Rating (My)	221 N-m
Yaw Moment Load Rating, 2 Bearings (My2)	1049 N-m
Roll Moment Load Rating (Mr)	251 N-m
For Use With	H20 series rails

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/H20FSSG0.pdf>
See store item page for other formats.