

H8064HFNL-P10 Cut Sheet



Integra Premium series enclosure, NEMA 1/2/3/3R/3S/4/4X/12/13, 8 x 6 x 4in (HxWxD), wall mount, polycarbonate, light gray, gloss finish, single-door, glass-filled nylon quick-release latch, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H8064HFNL-P10>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Integra |
| Item | Enclosure |
| Series | Premium |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 1/2/3/3R/3S/4/4X/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 8 x 6 x 4in (HxWxD) |
| Enclosure Height | 8.44in |
| Enclosure Width | 6.44in |
| Enclosure Depth | 4.71in |
| Mounting | Wall |

| | |
|---------------------------------|--|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | Polycarbonate |
| Color | Light gray |
| Finish | Gloss |
| Cover Type | Single-door |
| Latch Type | Glass-filled nylon quick-release latch |
| Padlock Attachment Type | Padlock hasp and staple |
| Padlockable | Yes |
| Keylocking | No |
| Includes | (2) mounting flanges |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E207562 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/H8064HFNL-P10.pdf>
See store item page for other formats.