

# HBBVP-01L-WNL Cut Sheet



Bimetallic pressure relief vent plug, M12 x 1.5mm thread type, stainless steel, 2,000 mL/min @ 70 mBar (1 psi), IP67 IP68, UL Type 4X, 12 and 13.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HBBVP-01L-WNL>

## Technical Specifications

<b>Brand</b>	Bimed
<b>Item</b>	Pressure relief vent plug
<b>Thread Type</b>	M12 x 1.5mm
<b>Thread Length</b>	10mm
<b>Material</b>	Stainless steel
<b>Free Airflow</b>	2,000 mL/min @ 70 mBar (1 psi)
<b>Water Intrusion Pressure</b>	0.2 bar (3 psi)
<b>IP Rating</b>	IP67 IP68
<b>Operating Temperature</b>	-20 to +100 deg C
<b>UL Type</b>	4X, 12 and 13
<b>Includes</b>	Washer and lock nut
<b>Additional Information</b>	Use 17mm wrench size

## Agency Approvals

<b>UL Recognized File #</b>	E350312
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/HBBVP-01L-WNL.pdf>  
See store item page for other formats.