

# HLM-EX-174015 Cut Sheet



IDEM safety limit switch, hazardous location rated, side rotary lever with stainless steel roller, (2) N.C. safety output(s), (2) N.O. monitoring output(s), slow action break before make, die-cast zinc aluminum, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HLM-EX-174015>

## Technical Specifications

<b>Brand</b>	IDEM
<b>Item</b>	Safety limit switch
<b>Switch Type</b>	IEC
<b>Actuator Type</b>	Side rotary lever with stainless steel roller
<b>Head Type</b>	90-degree adjustable
<b>Safety Output Type</b>	(2) N.C.
<b>Monitoring Output Type</b>	(2) N.O.
<b>Action</b>	Slow action break before make

<b>Reset</b>	No
<b>Body Width</b>	40mm
<b>Material</b>	Die-cast zinc aluminum
<b>IP Rating</b>	IP67
<b>Connection</b>	Pigtail
<b>Conductor Size</b>	24 AWG
<b>Cable Length</b>	9.8ft/3m

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HLM-EX-174015.pdf>  
See store item page for other formats.