

# HLM-SS-175011 Cut Sheet



IDEM safety limit switch, side rotary lever with stainless steel roller, (1) N.C. safety output(s), (1) N.O. monitoring output(s), snap action, 316 stainless steel, 1/2in female NPT conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HLM-SS-175011>

## Technical Specifications

<b>Brand</b>	IDEM
<b>Item</b>	Safety limit switch
<b>Switch Type</b>	IEC
<b>Actuator Type</b>	Side rotary lever with stainless steel roller
<b>Head Type</b>	90-degree adjustable
<b>Safety Output Type</b>	(1) N.C.
<b>Monitoring Output Type</b>	(1) N.O.
<b>Action</b>	Snap action
<b>Reset</b>	No
<b>Body Width</b>	41.6mm
<b>Material</b>	316 stainless steel
<b>IP Rating</b>	IP67 IP69K
<b>Connection</b>	1/2in female NPT conduit

## Agency Approvals

<b>UL Listed File #</b>	E258676
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>