

HLM-SS-EX-175015 Cut Sheet



IDEM safety limit switch, hazardous location rated, side rotary lever with stainless steel roller, (2) N.C. safety output(s), (2) N.O. monitoring output(s), slow action break before make, 316 stainless steel, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HLM-SS-EX-175015>

Technical Specifications

Brand	IDEM
Item	Safety limit switch
Switch Type	IEC
Actuator Type	Side rotary lever with stainless steel roller
Head Type	90-degree adjustable
Safety Output Type	(2) N.C.
Monitoring Output Type	(2) N.O.
Action	Slow action break before make
Reset	No
Body Width	41.6mm
Material	316 stainless steel
IP Rating	IP67 IP69K
Connection	Pigtail
Conductor Size	24 AWG
Cable Length	9.8ft/3m

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document