


HM-2BG Cut Sheet



NITRA air manifold base, aluminum alloy, 145 psi (10 bar) maximum operating pressure, G3/8 female BSPP outlet(s), bottom orientation. For use with ISO 5599/1 size 2 solenoid valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HM-2BG>

Technical Specifications

Brand	NITRA
Item	Air Manifold base
Material	Aluminum alloy
Maximum Operating Pressure	145 psi (10 bar)
Outlet Port	G3/8 female BSPP
Hole Orientation	Bottom
For Use With	ISO 5599/1 size 2 solenoid valves
Includes	Assembly clamps and seals

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document