

HMICVR1008C Cut Sheet



Stahlin SolarShield series HMI cover, NEMA 4/4X, 10.38 x 13.13 x 2.50in, polycarbonate, Pantone 428 C glacier gray, polycarbonate window. For use with HMIs up to 8x10in (HxW).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HMICVR1008C>

Technical Specifications

Brand	Stahlin
Item	HMI cover
Series	SolarShield
NEMA Rating	4/4X
Door Size	10.38 x 13.13 x 2.50in
Door Material	Polycarbonate
Color	Pantone 428 C glacier gray

Cutout Size	9.88 x 7.25in
Latch Type	1/4-turn wing handle
Gasket Type	Poured-in-place polyurethane
Window Material	Polycarbonate
Window Size	7.25 x 9.88in
For Use With	HMIs up to 8x10in (HxW)
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	E64358
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HMICVR1008C.pdf>
See store item page for other formats.