

# HMICVR1611C Cut Sheet



Stahlin SolarShield series HMI cover, NEMA 4/4X, 14.36 x 19.10 x 2.59in, polycarbonate, Pantone 428 C glacier gray, polycarbonate window. For use with HMIs up to 11x16in (HxW).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HMICVR1611C>

## Technical Specifications

Brand	Stahlin
Item	HMI cover
Series	SolarShield
NEMA Rating	4/4X
Door Size	14.36 x 19.10 x 2.59in
Door Material	Polycarbonate
Color	Pantone 428 C glacier gray

Cutout Size	11.25 x 15.88in
Latch Type	1/4-turn wing handle
Gasket Type	Poured-in-place polyurethane
Window Material	Polycarbonate
Window Size	11.25 x 15.88in
For Use With	HMIs up to 11x16in (HxW)
Includes	Mounting hardware

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E540056
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/HMICVR1611C.pdf>  
See store item page for other formats.