

HMICVR2014C Cut Sheet



Stahlin SolarShield series HMI cover, NEMA 4/4X, 17.33 x 23.07 x 2.59in, polycarbonate, Pantone 428 C glacier gray, polycarbonate window. For use with HMIs up to 14x20in (HxW).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HMICVR2014C>

Technical Specifications

Brand	Stahlin
Item	HMI cover
Series	SolarShield
NEMA Rating	4/4X
Door Size	17.33 x 23.07 x 2.59in
Door Material	Polycarbonate
Color	Pantone 428 C glacier gray

Cutout Size	14.25 x 19.88in
Latch Type	1/4-turn wing handle
Gasket Type	Poured-in-place polyurethane
Window Material	Polycarbonate
Window Size	14.25 x 19.88in
For Use With	HMIs up to 14x20in (HxW)
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	E540056
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HMICVR2014C.pdf>
See store item page for other formats.