

# HN0321S0304 Cut Sheet

CCEA Herionova series LED light bar, 458mm length, 24 VDC operating voltage, daylight white, recessed mount, pigtail, anodized aluminum body, 9.8ft/3m cable length, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HN0321S0304>



## Technical Specifications

|                          |                   |
|--------------------------|-------------------|
| <b>Brand</b>             | CCEA              |
| <b>Item</b>              | LED light bar     |
| <b>Series</b>            | Herionova         |
| <b>Length</b>            | 458mm             |
| <b>Operating Voltage</b> | 24 VDC            |
| <b>LED Color</b>         | Daylight white    |
| <b>Color Temperature</b> | 5000K             |
| <b>Mounting</b>          | Recessed          |
| <b>Connection</b>        | Pigtail           |
| <b>Power Consumption</b> | 40W               |
| <b>Body Material</b>     | Anodized aluminum |
| <b>Cable Length</b>      | 9.8ft/3m          |
| <b>IP Rating</b>         | IP67              |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E506617                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HN0321S0304.pdf>  
See store item page for other formats.