

HPX1-EHRN3R-GY1 Cut Sheet



IronHorse rotary handle, selector, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3R, IP65. For use with HMMP-32H manual motor manual motor protectors. 115mm shaft, operator and mounting screws included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPX1-EHRN3R-GY1>

Technical Specifications

Brand	IronHorse
Item	Handle
Handle Type	Rotary
Handle Style	Selector
Color	Black
Mounting	External front
Number Of Positions	2
Lockable Positions	ON-OFF
Defeatable	Yes
NEMA Rating	3R
IP Rating	IP65
For Use With	HMMP-32H manual motor manual motor protectors
Includes	115mm shaft, operator and mounting screws

Agency Approvals

UL Listed File #	E195426
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HPX1-EHRN3R-GY1.pdf>
See store item page for other formats.